


REAR VIEW



- | | |
|--------------------------------|-------------------------------|
| ① INTELLISLOT PORT | ⑦ INPUT CIRCUIT BREAKER 20A |
| ② USB PORT | ⑧ INPUT POWER PLUG (L6-30P) |
| ③ RS485 PORT | ⑨ OUTPUT CIRCUIT BREAKER 20A |
| ④ RS232 PORT | ⑩ OUTPUT POWER PLUG (L6-30R) |
| ⑤ TERMINAL BLOCK COMMUNICATION | ⑪ OUTPUT CIRCUIT BREAKER 15A |
| ⑥ EXTERNAL BATTERY CONNECTOR | ⑫ OUTPUT POWER CABLE (L6-15R) |

NOTES:

1. UNIT DIMENSIONS (WxDxH): 16.9" x 21.3" x 3.3" (2U)
(430mm) x (541mm) x (85mm)
2. UNIT WEIGHT: 71.4lbs (32.4kg)
3. SHIPPING DIMENSIONS (WxDxH): 22.4" x 28.2" x 10.3"
(570mm) x (717mm) x (262mm)
4. SHIPPING WEIGHT: 86lbs (39kg)
5. MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm)
FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1	<p style="text-align: center;">OUTLINE DRAWING LIEBERT GXT5 3000VA 208VAC RACK/TOWER UPS</p>					
CHK BY L. JOHNSON	ECN NO.		DWG. NO. GXT5-3K630HV_OD	DATE 10/29/19	REV. # 1	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229	
REF. DWG.	ORDER NO.		FILE NAME: \\p:\general\GXT5\Submittals\VA\Outline Draw\GXT5-3K630HV_OD				