



**FRONT VIEW**



**REAR VIEW**



**SIDE VIEW**

- ① INTELLISLOT PORT
- ② USB PORT
- ③ RS485 PORT
- ④ RS232 PORT
- ⑤ TERMINAL BLOCK COMMUNICATION
- ⑥ EXTERNAL BATTERY CONNECTOR
- ⑦ 20A INPUT CIRCUIT BREAKER
- ⑧ INPUT POWER PLUG AND CABLE C20
- ⑨ OUTPUT CIRCUIT BREAKER
- ⑩ PROGRAMMABLE OUTPUT RECEPTACLES (IEC 60906-1 10A)
- ⑪ NON-PROGRAMMABLE OUTPUT RECEPTACLES (IEC 60906-1 10A)

**NOTES:**

1. UNIT DIMENSIONS (WxDxH): 16.9" x 21.3" x 3.3" (2U)  
(430mm) x (541mm) x (85mm)
2. UNIT WEIGHT: 62lbs (28.2kg)
3. SHIPPING DIMENSIONS (WxDxH): 22.4" x 28.2" x 10.3"  
(570mm) x (717mm) x (262mm)
4. SHIPPING WEIGHT: 79.2lbs (36kg)
5. MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm)  
FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY L. JOHNSON	ECN NO.
REF. DWG.	ORDER NO.

OUTLINE DRAWING  
LIEBERT GXT5 3000VA BRAZIL  
230VAC RACK/TOWER UPS

DWG. NO. GXT5-3000IB_OD	DATE 5/12/20	REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229
----------------------------	-----------------	-------------	---

FILE NAME: I:\dpgeng\GXT5\Submittals(A)\Outline Dwg\GXT5-3000IB\_OD

