LIMITED WARRANTY FOR SITESCAN PRODUCTS



This Warranty is given by Vertiv Corporation (referred to herein as "Vertiv") **ONLY** to purchasers who buy for commercial or industrial use in the ordinary course of each purchaser's business.

General

Please read your Warranty carefully. This Warranty sets forth our responsibilities in the unlikely event of defect and tells you how to obtain performance under this Warranty.

ONE YEAR LIMITED WARRANTY

PRODUCTS COVERED

Sitescan Centralized Monitoring Software and SiteScan Monitoring Hardware

Terms of Warranty

As provided herein, the Vertiv product, exclusive of any PC component, is warranted to be free of defects in material and workmanship for a period of one year from the date of Warranty Inspection, not to exceed eighteen months from the date of product shipment, if product Warranty Inspection was performed by Vertiv authorized personnel. The Warranty Inspection date will be determined only from the product Warranty Inspection tag completed by Vertiv service personnel. In all other instances, the Vertiv product is warranted to be free of defects in material and workmanship for a period of one year from the date of product shipment by Vertiv. The date of shipment will be determined only from the Vertiv bill of lading. If any part or portion of the Vertiv product fails to conform to the Warranty within the Warranty period, Vertiv, at its option, will furnish new or factory remanufactured products for replacement of that portion or part.

Warranty Extends to First Purchaser for Use, Non-transferable

This Warranty is extended to the first person, firm, association or corporation for whom the Vertiv product specified herein is originally installed for use (the "User") in the fifty United States or Canada. This Warranty is not transferable or assignable without the prior written permission of Vertiv.

Assignment of Warranties

Vertiv assigns to User any warranties which are made by manufacturers and suppliers of components of, or accessories for, the Vertiv product and which are assignable, but Vertiv makes NO REPRESENTATIONS as to the effectiveness or extent of such warranties, assumes NO RESPONSIBILITY for any matters which may be warranted by such manufacturers or suppliers and extends no coverage under this Warranty to such components or accessories.

Drawings, Descriptions

Vertivwarrants for the period and on the terms of the Warranty set forth herein that the Vertiv product will conform to the descriptions contained in the certified drawings, if any, applicable thereto, to Vertiv's final invoices, and to applicable Vertiv product brochures and manuals current as of the date of product shipment ("Descriptions"). Vertiv does not control the use of any Vertiv product. Accordingly, it is understood that the Descriptions are NOT WARRANTIES OF PERFORMANCE and NOT WARRANTIES OF FITNESS FOR A PARTICUL AR PURPOSE.

Warranty Claims Procedure

Within a reasonable time, but in no case to exceed thirty (30) days after User's discovery of a defect, User shall contact Vertiv to request repair or replacement of the Vertiv product. Repair or replacement requests for products for which Vertiv performed Warranty Inspection shall be directed to Vertiv service at (800) Vertiv (543-2378). Vertiv designated personnel will repair or replace such products, without charge for materials or labor, subject to the limitations herein.

In all other instances, User shall contact Vertiv at 1-800-543-2378, within the above thirty (30) day time period, and request a return authorization number. Vertiv products shipped to Vertiv without a return authorization number will be refused and returned freight collect to User at User's expense. Vertiv products shipped by User to Vertiv which have incurred freight damage due to User's improper packaging of the product will not be covered by this Warranty and any repairs or replacement parts, components or products needed will be invoiced in the

full current price amount and returned freight collect to User. Subject to the limitations specified herein, Vertiv will repair or replace, at its option, without charge for materials, subsequent to its inspection and F.O.B. Vertiv's facility, the Vertiv product shipped to Vertiv with a return authorization number and warranted hereunder which does not conform to this Warranty. If replacement parts, components or products are shipped or caused to be shipped by Vertiv prior to inspection of the product claimed to be defective, the replacement parts, components or products shall be invoiced in the full current price amount and shipped freight collect F.O.B. Vertiv's facility. If Vertiv's inspection determines that the returned item(s) is covered by this warranty, User will be issued a credit in an amount equal to the price previously invoiced. Warranty coverage will be provided only after Vertiv's inspection discloses the claimed defect and shows no signs of treatment or use which would void the coverage of this Warranty, Replacement products shipped to User prior to User's shipment of the claimed defective product to Vertiv shall be invoiced in the full current price amount should User fail to return the claimed defective product to Vertiv within thirty (30) days of receipt of the replacement product.

All defective products and component parts replaced under this Warranty become the property of Vertiv.

Warranty Performance of Component Manufacturers

It is Vertiv's practice, consistent with its desire to remedy Warranty defects in the most prompt and effective manner possible, to cooperate with and utilize the services of component manufacturers and their authorized representatives in the performance of work to correct defects in the product components. Accordingly, Vertiv may utilize third parties in the performance of Warranty work, including repair or replacement hereunder. where, in Vertiv's opinion, such work can be performed in less time, with less expense, or in closer proximity to the Vertiv product.

Items Not Covered By Warranty

THIS WARRANTY DOES NOT COVER DAMAGE OR DEFECT CAUSED BY misuse, storage in an unsuitable environment, improper application, wrong or inadequate electrical current or connection, negligence, repair by non-Vertiv designated personnel, accident in transit, tampering, alterations, a change in location or operating use, exposure to the elements, Acts of God, theft or installation contrary to Vertiv's recommendations, or in any event if the Vertiv serial number or Warranty Inspection tag has been altered, defaced, or removed.

THIS WARRANTY DOES NOT COVER shipping costs, installation costs, circuit breaker resetting, maintenance or service items or any third-party labor or travel costs not authorized by Vertiv associated with the Vertiv product and further, except as may be provided herein, does NOT include labor costs or transportation charges arising from the replacement of the Vertiv product or any part thereof or charges to remove or reinstall the same at any premises of User.

THE PRODUCTS LISTED IN THIS WARRANTY ARE NOT FOR USE IN THE CONTROL AREA OR ANY REACTOR CONNECTED OR SAFETY APPLICATIONS OR WITHIN THE CONTAINMENT AREA OF A NUCLEAR FACILITY OR WHERE THE PRODUCTS HAVE POTENTIAL FOR DIRECT PATIENT CONTACT OR WHERE A SIX (6) FOOT CLEARANCE FROM A PATIENT CANNOT BE MAINTAINED AT ALL TIMES. THE PRODUCTS LISTED IN THIS WARRANTY MAY BE USED IN APPLICATIONS INVOLVING LIFE-SUSTAINING OR LIFE-SUPPORTING DEVICES ONLY WHERE THE END-USE CUSTOMER HAS SIGNED VERTIV'S HEALTHCARE APPLICATION SALES AGREEMENT, OTHERWISE THE WARRANTY IS VOID.

REPAIR OR REPLACEMENT OF A DEFECTIVE PRODUCT OR PART THEREOF DOES NOT EXTEND THE ORIGINAL WARRANTY PERIOD.

Limitations

THIS WARRANTY IS IN LIEU OF AND EXCLUDES ALL OTHER WARRANTIES. EXPRESS OR IMPLIED. INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

USER'S SOLE AND EXCLUSIVE REMEDY IS REPAIR OR REPLACEMENT OF THE VERTIV PRODUCT AS SET FORTH HEREIN.

IF USER'S REMEDY IS DEEMED TO FAIL OF ITS ESSENTIAL PURPOSE BY A COURT OF COMPETENT JURISDICTION, VERTIV'S RESPONSIBILITY FOR PROPERTY LOSS OR DAMAGE SHALL NOT EXCEED THE NET PRODUCT PURCHASE PRICE.

IN NO EVENT SHALL VERTIV ASSUME ANY LIABILITY FOR INDIRECT, SPECIAL, INCIDENTAL, EXEMPLARY OR CONSEQUENTIAL DAMAGES OF ANY KIND WHATSOEVER, INCLUDING WITHOUT LIMITATION LOST PROFITS, BUSINESS INTERRUPTION OR LOSS OF DATA, WHETHER ANY CLAIM IS BASED UPON THEORIES OF CONTRACT, NEGLIGENCE, STRICT LIABILITY, TORT, OR OTHERWISE.

Miscellaneous

NO SALESPERSON, EMPLOYEE, OR AGENT OF VERTIV IS AUTHORIZED TO ADD TO OR VARY THE TERMS OF THIS WARRANTY.

Vertiv obligations under this warranty are conditioned upon Vertiv timely receipt of full payment of the product purchase price and any other amounts due. Vertiv reserves the right to supplement or change the terms of this Warranty in any subsequent warranty offering to User or others.

In the event that any provision of this Warranty should be or becomes invalid and/or unenforceable during the Warranty period, the remaining terms and provisions shall continue in full force and effect.

This Warranty shall be governed by, and construed under, the laws of the State of Ohio, without reference to the conflict of laws principles thereof.

This Warranty represents the entire agreement between Vertiv and User with respect to the subject matter herein and supersedes all prior or contemporaneous oral or written communications, representations, understandings or agreements relating to this subject.



VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2018 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.

