



FRONT VIEW



REAR VIEW



SIDE VIEW

- | | |
|--------------------------------|---|
| ① INTELLISLOT PORT | ⑧ OUTPUT POWER PLUG (L5-30R) |
| ② USB PORT | ⑨ INPUT POWER PLUG (L5-30P, 10 FEET/3M) |
| ③ RS485 PORT | ⑩ OUTPUT CIRCUIT BREAKER |
| ④ RS232 PORT | ⑪ NON-PROGRAMMABLE OUTPUT RECEPTACLES (5-20R) |
| ⑤ TERMINAL BLOCK COMMUNICATION | ⑫ PROGRAMMABLE OUTPUT RECEPTACLES (5-20R) |
| ⑥ EXTERNAL BATTERY CONNECTOR | |
| ⑦ 30A INPUT CIRCUIT BREAKER | |

NOTES:

- UNIT DIMENSIONS (WxDxH): 16.9" x 21.3" x 3.3" (2U)
(430mm) x (541mm) x (85mm)
- UNIT WEIGHT: 66lbs (30kg)
- SHIPPING DIMENSIONS (WxDxH): 22.4" x 28.2" x 10.3"
(570mm) x (717mm) x (262mm)
- SHIPPING WEIGHT: 77.2lbs (35.1kg)
- MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm)
FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY L. JOHNSON	ECN NO.
REF. DWG.	ORDER NO.

OUTLINE DRAWING
LIEBERT GXT5 3000VA
100/120VAC RACK/TOWER UPS

DWG. NO. GXT5-3000LV_OD	DATE 10/29/19	REV. # 2	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229
----------------------------	------------------	-------------	---

FILE NAME: I:\dpgeng\GXT5\Submittals(A)\Outline Dwg\GXT5-3000LV_OD

